



INSTALLATION								Data Sheet		
CamHOSP 2 – Screentek Standards units								Reference	Index	Page
								FP.A.0750	B	1/1




Ceiling for operating theater
Easy installation
Safety mounting
Easy maintenance




Article number	Type	Size int. (AxBxH) en mm	Aera int. (m2)	Airflow m3/h			Nb of module	MEGALAM MD14 filters number			Shipping data	
				at 0,25 m/s	at 0,3 m/s	at 0,45 m/s		3423.00.33	3423.05.46	3423.08.52	m³	kg
								560x560 x66	560x860 x66	560x1165 x66		
5526.10.00	Type Bed	1815x905x400	1,7	1300	1560	2350	1		3		0,66	40
5526.20.00	Type 2	1815x2419x400	4,4	3170	3800	5700	2+2	2	6		1,76	90
5526.30.00	Type 3	2422x2419x450	5,9	4350	5200	7800	4+2		10		2,64	125
5526.35.00	Type 3.5	3029x2422x450	7,3	5560	6780	10000	4+2		2	8	3,30	150
5526.40.00	Type 4	3027x3027x450	9,2	7050	8460	12700	4			12	4,12	150


(*) Without filter to be ordered separately




Type Bed
1,8 x 0,9 m




Type 2
1,8 x 2,4 m



Type 3
2,4 x 2,4 m



Type 3.5
3 x 2,4m



Type 4
3 x 3 m

Specifications :

Type :

Construction :

Assembling :

Protection :

Test port :

Filter mounting :

Housing airtighness at 450Pa:

Gasket seat airtighness at 450Pa :

Operating light path :

Finishing:

Installation:

Options:

Modular ceiling unidirectional airflow for operating theaters

Modular, each module is factory assembled and caulked including:

• 1 steel plenum

• 1 airtight platform full welded

• 1 mounting kit

Modules are assembled on site by bolts

Mechanical airtightness between module by gasket

Epoxy painted RAL 9010, inside and outside

1 room side, for pressure and EMERY test sampling

Filter access from room side, quick clamping device by prepositionned unlosable clamps, with compression limitation

Class B according to NF EN 1886:1998

Class L1 (M) according to PR EN 1886:2003

Class C according to PR EN 12237:2003

Max local penetration less than 10⁻⁴ (0.01 %) according to ISO EN 14644-3


Airtight

3 possibilities (Screentek, Protek, Teknik) see FPA0751

Suspended by hangers to fix into peripheral perforated pads

• Airflow guide (see FPA0756)

• After sales mounting kit art. Number 5526.99.03



FARR

CAMFIL 77/81 Bd de la République – 92257 LA GARENNE COLOMBES CEDEX France

Tél. 01.46.52.48.00 – Fax : 01.47.60.17.81

FPA0750-B.doc



CAMFIL 77/81 Bd de la République – 92257 LA GARENNE COLOMBES CEDEX France

Tél. 01.46.52.48.00 – Fax : 01.47.60.17.81

FPA0750-B.doc